

PERFORMANCE DATA

Unit Size (in.)	Airflow (cfm)	Filter	Static Pressure (in. w.g.)	
24 x 24	220	HEPA 99.99% (.3µm) 2" Pack Depth	0.42	
	285		0.52	
	315		0.57	
	24 x 24	220	HEPA 99.99% (.3µm) 4" Pack Depth	0.28
		285		0.37
		315		0.4
	24 x 24	220	ULPA 99.9995% (.12µm) 2" Pack Depth	0.48
		285		0.61
		315		0.68
	24 x 24	220	ULPA 99.9995% (.12µm) 4" Pack Depth	0.32
		285		0.4
		315		0.45
24 x 36	345	HEPA 99.99% (.3µm) 2" Pack Depth	0.42	
	445		0.52	
	495		0.57	
	24 x 36	345	HEPA 99.99% (.3µm) 4" Pack Depth	0.28
		445		0.37
		495		0.4
	24 x 36	345	ULPA 99.9995% (.12µm) 2" Pack Depth	0.48
		445		0.61
		495		0.68
	24 x 36	345	ULPA 99.9995% (.12µm) 4" Pack Depth	0.32
		445		0.4
		495		0.45
24 x 42	410	HEPA 99.99% (.3µm) 2" Pack Depth	0.42	
	525		0.52	
	585		0.57	
	24 x 42	410	HEPA 99.99% (.3µm) 4" Pack Depth	0.28
		525		0.37
		585		0.4
	24 x 42	410	ULPA 99.9995% (.12µm) 2" Pack Depth	0.48
		525		0.61
		585		0.68
	24 x 42	410	ULPA 99.9995% (.12µm) 4" Pack Depth	0.32
		525		0.4
		585		0.45
24 x 48	475	HEPA 99.99% (.3µm) 2" Pack Depth	0.42	
	610		0.52	
	680		0.57	
	24 x 48	475	HEPA 99.99% (.3µm) 4" Pack Depth	0.28
		610		0.37
		680		0.4
	24 x 48	475	ULPA 99.9995% (.12µm) 2" Pack Depth	0.48
		610		0.61
		680		0.68
	24 x 48	475	ULPA 99.9995% (.12µm) 4" Pack Depth	0.32
		610		0.4
		680		0.45

Performance Notes:

1. Static Pressure, in. w.g., required at inlet for the listed cfm.
2. Air flow in cubic feet per minute, cfm.